



## **BENEFITS**

- Mitigates Risk: Screen for elevated skin-temperature before an employee or visitor enters the building.
- Improves Morale: Facilitates a safer environment for employees and visitors.
- Lowers Costs: Easy automated operation improves efficiency.

## MINMOE TOUCHLESS ACCESS CONTROL TERMINAL WITH TEMPERATURE

Hikvision's new Wi-Fi enabled Temperature Screening Terminal DS-K1T341BMWI-T is a budget-friendly, touchless access control device integrated with thermographic temperature screening and mask detection.

It's a great solution to enable safe operations for small businesses, including restaurants, markets and grocers, coffee shops, gyms and boutiques.

The terminal uses a Wi-Fi connection and power outlet, enabling easy installation and flexible placement. It is equipped with 2.4GHz Wi-Fi which can be deployed anywhere with a wireless connection and power outlet.

The 4.3-inch LCD touch screen simplifies configuration and user interaction, and it integrates with Hikvision NVRs for live view and playback. It quickly measures skin-surface temperature and displays it on the 4.3-inch touch screen LCD.

#### Key features include:

- Cost-effective, touch-free access control
- Wi-Fi enabled for flexible installation
- Built-in temperature screening and mask detection
- All-in-one solution combines touchless access control, skin-surface temperature measurement, and mask detection



DS-K1T341BMWI-T

## **ACCURATE & AFFORDABLE TEMPERATURE SCREENING**

Designed for customers who want to ensure safety while operating on a discerning budget, the 4.3-inch touchless terminal rapidly screens skin-surface temperature using thermographic technology and provides face mask detection with audible alerts. The terminal uploads abnormal temperature event records for easy reporting and tracking.


#### The terminal features:


- Temperature measurement range: 86° to 113° F (30° to 45° C)
- Accuracy up to ±0.9° F (±0.5° C)
- Temperature measurement distance: 0.98 feet to 3.3 feet (0.3 m to 1 m)
- · Fast temperature measurement mode
- · Multiple authentication modes
- · Face mask detection features, including face mask alert & forced mask wearing alert
- · Built-in Mifare card reading module
- 3,000-person capacity, 5,000 Mifare card capacity, and 100,000 event capacity
- View temperature results on local screen for quick identification
- · No need to set permissions, normal temperature will unlock the door

The terminal is equipped with a 2 MP wide-angle dual-lens, an anti-spoofing feature where an individual cannot be granted access by holding up a photograph. Important access control interfaces include a lock relay, request to exit (REX), Wiegand, RS485 and a tamper alarm.

Our Temperature Screening Terminal supports multiple authentication modes including access control card with normal temperature, ID with normal temperature. Both can be combined with the use of mask detection. During the temperature screening process, an audible warning will alert if no mask is detected and the person will be denied entrance until a mask is detected.

Hikvision's thermographic skin-temperature screening technology sets it apart from competitors. See the chart below for Hikvision advantages.





# OPTIONAL VIDEO INTERCOM MONITORING TABLET DS-KC001



### **Video Monitoring Tablet Simplifies Temperature Screening**

Using our Video Intercom Monitoring Tablet DS-KC001 with our Temperature Screening Terminal simplifies monitoring of security and temperature. The tablet is equipped with a 7-inch color touch screen LCD and a built-in 32 GB SD card that can record up to 100,000 temperature records and events. Abnormal temperature alarms and temperature records are sent to the monitoring tablet in real-time, allowing onsite personnel to quickly identify anyone with elevated skin-surface temperature and take immediate action to comply with guidelines.

Temperature Screening + Access Control + Video Surveillance = Versatile and Precise Monitoring Solution

- 7-inch Touch Screen Android Monitoring Tablet
- Display Resolution: 1024x600; Wi-Fi 802.11b/g/n
- Remote Temperature Screening and Records Checking with Real-Time Preview
- Centralized Data Management up to 100,000 Records
- · Built-in 32 GB SD card
- Abnormal Temperature Alarm
- · Remote Access Control and Video Intercom
- Power Adaptor Included

Model Operating System		DS-K1T341BMWI-T Linux
Resolution	120 × 160	
Frame Rate	25 fps	
Temperature Range	86 °F to 113 °F (30 °C to 45 °C)	
Temperature Accuracy	±0.9° F (±0.5 °C)	
Measuring Distance	0.98 to 3.3ft (0.3 to 1.0 m)	
Screen	Screen	4.3-inch touch screen
	Resolution	272 x 480
Camera	2 MP dual-lens camera	
Indicator	Supported	
Network	Wired	10/100 Mbps self-adaptive
	Wireless	2.4GHz Wi-Fi
Capacity	Person	3,000
	Mifare Card	5,000
	Event	100,000
Interface	Network Interface	1
	RS-485	1
	Wiegand	1
	Lock Relay	1
	Exit Button (REX)	1
	<b>Door Contact Input</b>	1
	Tamper	1
Card Enrollment	Card Type	Mifare 1 Card
	Card Reading Distance	0 to 2 inches (0 to 5 cm)
	Card Reading Duration	<1s
	Person Reading Duration	<0.2s
Function	Person Anti-Spoofing	Supported
	Audio Prompt	Supported
General	Operating Voltage	12 VDC/2 A (Included)
	Operating Temperature	32°F to 122°F (0°C to 50°C)
	Operating Humidity	10 to 90% (non-condensing)
	Power Consumption	<15 W
	Dimensions	3.35" x 8.94" x 1.2" (85 mm × 227 mm × 30 mm)
Installation	Wall Mount Brackets	Wall Mount Plate (included, single gang box compatible)
	Floor Stand	DS-KAB671-B (Optional)
	Floor Stand Base	DS-KAB6-BASE (Optional)

## FOCUSED ON YOUR SUCCESS



\*Disclaimer: Hikvision Highly Accurate Thermographic Cameras and Terminals (HAT Cameras and Terminals) are not FDA-cleared or approved thermal imaging devices intended to measure human skin-surface temperature. The HAT Cameras and Terminals are not intended for use in diagnosis of disease or other conditions, or in the cure, mitigation, treatment, or prevention of disease, and shall not be solely or primarily used as an effective diagnostic device for COVID-19. Elevated body temperature should be confirmed with secondary evaluation methods (e.g., an NCIT or clinical grade contact thermometer). Users, through their experience with the Hikvision HAT Cameras and Terminals in the particular environment of use, should determine the significance of any fever or elevated temperature based on the skin telethermographic temperature measurement. Visible thermal patterns are only intended for locating the points from which to extract the thermal measurement.

To ensure the accuracy of the human skin-surface temperature measurement, the technology shall be used to measure only one subject's temperature at a time and shall not be used to measure multiple individuals'

temperatures simultaneously.